


piSAVE Sense Flow Characteristics

Vacuum flow (scfm)



piSAVE® sense Multiple port fitting 02/60 (yellow) and 03/60 (green) are mainly suitable for sealed and smooth materials, such as metal and glass.

Description	Unit	Sense valve			
		02/60	03/60	04/60	05/60
Pump flow/cup to close valve	scfm	0.44 (@ 0.9 -inHg)	0.78 (@ 0.9 -inHg)	1.17 (@ 2.1 -inHg)	1.53 (@ 3.2 -inHg)
Pump flow/cup minimum	scfm	0.002 (@ 13 -inHg)	0.13 (@ 13 -inHg)	0,32 (@ 13 -inHg)	0.53 (@ 13 -inHg)